


REHAU 2K-D foam quantity requirements



An estimation of the quantity of 2K-D foam cans required for each REHAU shroud. This may vary due to the size of the pipes and fittings installed within the shroud.

CLIP-FLEX Shroud



| Shroud size | Pipe outer diameter (mm) | 2K-D foam cans required (approx.) |
|-------------|--------------------------|-----------------------------------|
| I-small | 90 – 120 | 1.5 cans |
| | 125 – 150 | 1 can |
| L-small | 90 – 120 | 1 can |
| | 125 – 150 | 1 can |
| T-small | 90 – 120 | 2 cans |
| | 125 – 150 | 1.5 cans |
| | 160 – 175 | 3.5 cans |
| I-large | 180 – 210 | 3 cans |
| | 225 – 250 | 2.5 cans |
| | 160 – 175 | 3 cans |
| L-large | 180 – 210 | 2.5 cans |
| | 225 – 250 | 2 cans |
| | 160 – 175 | 5 cans |
| T-large | 180 – 210 | 4 – 5 cans |
| | 225 – 250 | 3 – 4 cans |

Heat shrink shroud



| Foam size | Shroud size | Foam volume (litres) | 2K-D foam cans required (approx.) |
|-----------|-------------|----------------------|-----------------------------------|
| 5 | I-small | 10 – 11 | 1 can |
| 6.2 | L-small | 14 – 15 | 1.5 cans |
| 7 | T-small | 17 – 19 | 2 cans |
| 8 | I-large | 22 – 24 | 2 cans |
| 8.1 | L-large | 25 – 27 | 2.5 cans |
| 9.1 | T-large | 31 – 34 | 3 cans |

RAUTHERMEX clip shroud



| Foam size | Shroud size | Foam volume (litres) | 2K-D foam cans required (approx.) |
|-----------|------------------|----------------------|-----------------------------------|
| 5 | I-small, L-small | 10 – 11 | 1 can |
| 6.2 | T-small | 14 – 15 | 1.5 cans |
| 8 | I-large, L-large | 22 – 24 | 2 cans |
| 9.1 | T-large | 31 – 34 | 3 cans |

Please refer to each individual shroud installation instructions before starting the installation. A safety datasheet for the 2K-D foam is provided on each can via a QR-code.

